



Technical Data Sheet

IP Basic

Parameters	Standard	Unit	Measurement
Substance	ISO 536	g/m ²	80 +/- 3
Thickness	ISO 534	µm	104 +/- 3
Bulk	ISO 534		1,3
Moisture Content	ISO 287	%	3,6 - 5,0
Roughness	ISO 8791	Bendtsen ml/min	220 +/- 60
Whiteness	ISO 11475	CIE	146 +/- 3
Brightness D65	ISO 2470-2	%	105 +/- 2
Opacity	ISO 2471	%	92 +/- 2
Stiffness MD	ISO 2493	m/N	106 +/- 15
Stiffness CD	ISO 2493	m/N	50 +/- 15

Production sites:

The production mills operate in compliance with the following standards



Special Attributes:



References:
 Product is made taking into account requirements of DIN EN 12281
 Product made from ECF Pulp
 ISO 18001 - OHSAS Health & Safety

The data presented can be changed without notice.

International Paper EMEA
 Chaussée de la Hulpe 166
 1170 Brussels, Belgium
 Tel.: +32 2 774 1211
 Fax: +32 2 774 1299
 Extract date: 28.09.2017