

Article: ISS-1040

Polyester, glassfilled

rated voltage AC/DC: 600 / 750 V

dielectric strength: 10 KV/ mm

length L (in mm): 40

thread H1+H2: M10

Material: Polyester, glassfilled

outside diameter D1 (in mm): 30

length of thread (mm): 12

wrench size: hexa38

spec. weight: 1,9

share of glassfilling: 15%

tensile strength: 400 kg f / cm


bending strength: 900 kg f / cm

pressure resistance: 1500 kg f / cm

impact strength: 250 J / m

temperature resistance: til 80 °C

RoHS-konform

Material: DMC  UL 94 V-0  
 Alle Isolatoren sind  zertifiziert