

Quick-Ohm item number:

Distance H (in mm):

Material:

Nominal Voltage AC/DC:

HEX A/F:

2 x female thread:

Inserts:

Heat Resistance:

Specific Gravity:

Glass Contents:

Water Absorption (24hrs):

Tensile Strength:

Flexural Strength:

Compressive Strength:

Impact Strength Izod::

Dielectric Strength:

ARC Resistance:

Comparative Tracking Index (CTI):

Flammability UL-94:

IS20HH630

30

Dough Molding Compound (DMC) „DR20“

1200 / 1600 V

SW20 full hex

M6 x 7mm

Steel, zinc passivated

-40°C til +135 °C

1,9

15%

0,15%

400 kg f/cm²

900 kg f/cm²

1500 kg f/cm²

250 J/m

10 kV/mm

+180 Secs

+600 Volts

V-0, E249670/E314972

RoHS-konform

