

# DeTeWe Outdoor 8000 (Duo Case)

## Dripping water protected PMR (Private Mobile Radio) 2-way radio set

This 2-way radio set is suitable for the use in case of high requirements. Due to dripping water protection it is ideal for challenging use in the building and craft sector (e. g. road construction or market garden), for sport activities or for events. Its eye-catching orange colour makes it easy to find it if you have misplaced it or if it fell down or out of your pocket. With a range of 9 km it bridges even long distances.



### Characteristics:

- Dripping water protected (IPX2 standard) \*
- No licence fee or airtime charges
- Backlit display
- Lower power mode
- Scan function (find partner after change of channel or other 2-way radios within your grasp)
- Dual Channel Monitor function (signalling of radio activities on the activated and a second channel)
- VOX function (voice operated transmission without and with headset)
- Automatic Squelch (fixed limit at which signal strength noise limiter is opening)
- Embedded compander for crystal clear sound
- Call function (sending signal 3 seconds)
- Roger Beep function (signalling of an ended call)
- 8 level volume control
- 5 call tones
- Battery charge level indicator
- Acoustic low battery warning
- Timer
- Keyboard lock
- Special headset (Air Tube headset) for strong fixation and good shield against noises
- Removable belt clip

### Technical Data:

- Range up to 9 km (depending on terrain and conditions)
- 8 channels
- 38 CTCSS subchannels (special ton frequencies)
- 0,5 watt output power
- Channel frequency 446 MHz

### Contents:

- 2 2-way radios
- 2 belt clips
- 2 rechargeable battery packs
- 2 special headsets (air tube headsets)
- 1 desktop charger
- 1 power supply
- 1 instruction manual
- 1 transport- and safekeeping case



### Item number:

- Item number: 208046
- European Article Number: 4260117670626