



CLIENT NO.	CLIENT NO.	LENGTH
44074		1.5M
44075		3.0M
44076		5.0M
44078		10.0M

PRINTING :  
**VIVANCO** 75Ω COAXIAL CABLE TRIPLE SHIELDED  
ca.218mm **VIVANCO**

CABLE SPECIFICATION (ROHS) SHIELDING :>110DB	
CONNECTOR	AS DRAWING
WIRE	1.Conductor :0.64±0.05mm Cu
	2.Insulation : 3.6±0.2mm FPE
	3.Shield:singled 0.03/14 mm Al-foil
	4.Braid:112B/0.12±0.01mm magnalium
	5.Shield:double 0.06/14mm AL-foil
	6.Pvc jacket: OD .6.0 ± 0.2MM /WHITE
FERRITE	TWO/ WHITE COLOR

DATE: 2012-01-31