



4 port antenna wall outlet CATV | SAT | SAT

premium-line

- terminal type
- suitable for return path 5...65 MHz
- easy to mount, new and improved cable fixation, fold-away clamping-cover
- extended F sockets
- digital-compatible
- for terrestrial TV and satellite TV



Article	SSD 7-00
Part No.	SSD00700
	 
Tap method	Filter circuit/directional coupler
Frequency range	5...2200 MHz
TV connector (forward path returnpath)	109...862 MHz 5...65MHz
Tap loss (forward path returnpath)	= 2 dB = 2 dB
Radio connector	87,5...108 MHz
Tap loss	= 2 dB
SAT connectors (right left)	950...2200 MHz 950...2200 MHz
Tap loss	= 2 dB = 2 dB
Isolation intern	= 30 dB
DC power pass/trunk	yes
Usable cables	0,63...1,13 mm inner conductor 4,70...7,35 mm outer diameter
Dimensions appr.	78 x 78 x 46 mm
Available accessories	
Surface frame TZU 1-xx more...	Cover plate SZU 2-xx more...

Surface frame

- TZU 1-00 for one-part cover
- TZU 1-10 for two-part cover



Article	TZU 1-00	TZU 1-10
Part No.	TZU00100	TZU00110
Packing unit	1	
Dimensions	80 × 80 mm	75 × 75 mm
	for one-part cover	for two-part cover
Color	weiß	

Cover plates | single piece

- Dimensions 80 x 80 mm
- suitable for surface frame TZU 1-00



Article	SZU 2-00	SZU 2-01	SZU 2-02	SZU 2-03	SZU 2-04	TZU 2-00
Part No.	SZU00200	SZU00201	SZU00202	SZU00203	SZU00204	TZU00200
Packing unit	50					
Application	TV/R/ SAT	TV/R/ DATA	TV/R/ SAT/DATA	TV/R/ DATA/DATA	TV/R/ SAT/SAT	TV/R
	SSD 5-xx SSD 6-xx	BSD 963-xx	BSD 960-xx	BSD 961-xx	SSD 7-00	BSD 4- , 21-xx
Dimensions	80 x 80 mm					
Color	weiß					