

Wall Mounting Patch Brackets for 483 mm (19") Installations





Abstract

Wall mounting patch brackets for 483 mm (19") installations, variable depth, various height units, color grey (RAL 7035) or black (RAL 9005)

Features

- for installation of 483 mm (19") components
- 1.1 1.5 strong sheet steel, powder coated
- available in several height unit versions
- adjustable depth (min. 225 mm; max. 399 mm)
- with four holes for wall mounting
- rear side with cut-out e.g. for cabling
- Load capacity: 15 kg

Product Overview

The Wall Mounting Patch Brackets for 483 mm (19") installations are used for open mountings of 483 mm (19") components. They are available in several height units to suit to your individual needs of space. The brackets are adjustable in depth (from 225 mm up to 399 mm) which makes the installation of larger components possible. The rear side has a big cut-out area that can be used to guide cables which come directly from the wall.

Product Number Information

Item code	Height unit	Product dimensions (HxWxD) in mm	Color
DN-19 PB-2U	2U	94.1x528x225 mm	Grey (RAL 7035)
DN-19 PB-2U-SW			Black (RAL 9005)
DN-19 PB-4U	4U	183x528x225 mm	Grey (RAL 7035)
DN-19 PB-4U-SW			Black (RAL 9005)
DN-19 PB-8U	8U	360.8x528x225 mm	Grey (RAL 7035)
DN-19 PB-8U-SW			Black (RAL 9005)

Logistic Data

Height unit version	Packaging dimensions (HxWxD) in mm	Net weight in kg	Gross weight in kg
2U	97x250x530 mm	2.1 kg	2.3 kg
4U	190x250x530 mm	3.0 kg	3.3 kg
8U	380x250x530 mm	6.0 kg	6.5 kg

Assmann Electronic GmbH, Auf dem Schüffel 3, 58513 Lüdenscheid, Germany, info@assmann.com, printing errors, falsities and technical changes remain reserve



Technical Drawings









