

**NOTE:**

1. Electrical test:
  - (1). 100% open short & miss wire test;
  - (2). Insulation resistance: DC 300V 10MΩ;
  - (3). Contactor resistance: 3Ω Max;
  - (4). Dielectric strength: 100V AC/Minute, 1mA.
2. PRINT WORD: AWM STYLE 2725 80°C 30V VW-1 28AWG×1P 28AWG×2C
3. PACKING: 1PCS/PE BAG
4. ROHS AND REACH COMPLIANT

**MATERIAL LIST:**

④	OUTER MOLD	PVC COLOR FOR TRANSPARENT	2	
③	USB B TYPE	USB B/M SOLDER TYPE, WHITE PBT INSULATION, THE PIN GOLD PLATING, THE SHELL FOR NICKEL PLATING	1	
②	USB A TYPE	USB A/M SOLDER TYPE, WHITE PBT INSULATION, THE PIN GOLD PLATING, THE SHELL FOR NICKEL PLATING	1	
①	CABLE	USB2.0 28AWG (7/0.12BC)*IP+28AWG (7/0.12BC)*2C+AL-FOIL+ BRAID (16/3/0.12)AL-MG PVC/TRANSPARENT JACKET OD: 4.0±0.2MM	1	
NO.	PARTS NAME	SPECIFICATION STANDARD	QTY	REMARK

TEL: [REDACTED]; FAX: [REDACTED]	
CUSTOMER	ITEM NO. SEE THE CHART
PRODUCT NAME	UNO ITEM NO. UNIT MM
DRAWNBY	CHECKBY
FERGUS	APPOBY
DATE	2013.06.05
REV.	REV.

REVISION RECORD MODIFICATIONS

BY CHK

NEW

2013.06.05

A

DRAWNBY


CHECKBY

APPOBY

DATE

2013.06.05

ITEM NO.	LENGTH
	500+60/-0
	1000+60/-0
972030	1800+100/-0
972387	3000+100/-0
972317	5000+100/-0



TEL: [REDACTED]		SEE THE CHART	
CUSTOMER	[REDACTED]	ITEM NO.	UNIT
PRODUCT NAME	USB 2.0 AM/BM	UNO ITEM NO.	MM
DRAWNBY	CHECKBY	APPOBY	DATE
FERGUS			2013.06.05
BY	CHK	REVISION RECORD MODIFICATIONS	REV.
		NEW	A
		2013.06.05	DATE