



Revised By	Revision History	Date	Rev.
G. Chen	Release Digitus Format Drawing	Feb,20,2010	01
G.Chen	Revise the PIN Assignment	Oct,26,2011	02




Printing: **DIGITUS** Cat5e F-UTP PATCH CORD CAT5e ISO/IEC 11801 & TIA/EIA 568-B.2  
 GHMT certified [WWW.DIGITUS.INFO](http://WWW.DIGITUS.INFO) E213738 26AWG×4P CM (UL) C(UL)



**DK-1521-XXX-XX**  
 For Cable Length  
 For Cable Color

PIN ASSIGNMENT (T568B to T568B)		
P1 (T568B)	PIN NO.	P2 (T568B)
WHT ORG	1	WHT ORG
ORG	2	ORG
WHT GRN	3	WHT GRN
BLU	4	BLU
WHT BLU	5	WHT BLU
GRN	6	GRN
WHT BRN	7	WHT BRN
BRN	8	BRN



STICKER ON THE POLY BAG  
 (Printings in "Arial" Font)

DK-1521-XXX/X  
 PATCH CABLE, CAT.5E  
 F-UTP, x COLOR  
 Length: x meter

BAR CODE  
 EN CODE

CONDUCTOR	BAR COPPER 26AWG 7/0.16±0.015 MM	CABLE	F-UTP CAT.5E STRANDED 26AWG x 4P
DRAIN WIRE	AL-Magnesium wires(7/0.158±0.01mm)	PLUG	RJ45 8P8C GOLD-PLATED 3U" CONTACTS
INSULATION	Thickness: MIN At Any Point: 0.18 mm Max Average: 0.20 mm φ:0.86±0.1mm	LENGTH	One piece is packed into individual Digitus Polybag with sticker Sticker contents incl.: P/N, Product Description, Length, Barcode (EN code).
CABLE JACKET	PVC,Thickness:Min At anypoint: 0.53mm Max Average: 0.56mm φ: 5.2±0.3mm	CABLE COLOR	GREY 687#,BLACK 063#,RED 172#,GREEN 269#,BLUE 580#, YELLOW 367#,ORANGE 766#,WHITE 461#,PURPLE 965# ;

	Date	Name	Part No.
Drawn By	Feb,20,2010	Gary Chen	<b>DK-1521-XXX/XX</b>
Checked By	Oct,26,2011	Andreas.N	
Approved By			

Title:  
**DIGITUS CAT 5E FTP PATCH CABLE  
 STRANDED WIRES AWG26**



Scale	N/A	Sheet
Unit	MM	1/1

ST80211