




Signature	Revision History	Date	Rev.
G. ChEn	Release DIGITUS drawing format	Feb.22.2010	01



**DK-1531-XXX-X**  
 For Cable Length  
 For Cable Color



ORANGE	1	2	GREEN
WHITE/ORANGE		WHITE/GREEN	
BLUE	3	4	BROWN
WHITE/BLUE		WHITE/BROWN	

**PIN ASSIGNMENT**

PA/R	P1	(T568B)	P2	(T568B)
1	1	WHT/ORG	1	WHT/ORG
	2	ORG	2	ORG
2	3	WHT/GRN	3	WHT/GRN
	6	BLU	6	BLU
3	4	WHT/BLU	4	WHT/BLU
	5	GRN	5	GRN
4	7	WHT/BRN	7	WHT/BRN
	8	BRN	8	BRN

CONDUCTOR	BARE COPPER 26AWG 7/0.152±0.005MM	WIRE	CAT5E SF/UTP STRANDED WIRES 26AWG*4P
DRAIN WIRE	ALUMINUM MAGNESIUM WIRE	PLUG	RJ45 8P8C 3U" GOLD-PLATED CONTACTS
INSULATION	THICKNESS: MIN AT ANY POINT: 0.15MM MAX AVERAGE: 0.25MM Ø: 0.88±0.06MM	LENGTH	XX M
JACKET PVC	THICKNESS: MIN AT ANY POINT: 0.50MM MAX AVERAGE: 0.60MM DIAMETER: 5.6±0.2MM	JACKET COLOR	XXXX

Drawn By	Date	Name	Part No. <b>DK-1531-XXX-X</b>		
Feb-22-2010	G.ChEn				
Checked By	Feb-22-2010	Kevin.N			
Approved By			Title: DIGITUS PATCH CABLE CAT5E SF/UTP AWG26 STRANDED WIRES		
			Scale	N/A	Sheet
			Unit	MM	1/1

ST80211