






DB 9M(NICKEL PLATED)



DB 9F(NICKEL PLATED)




DB 9M TO DB 9F ADAPTER
BLACK MOLDING
Tolerance:±0.3mm




CONTACTS:

DB 9M	1	2	3	4	5	6	7	8	9	64
DB 9 F	1	2	3	4	5	6	7	8	9	64



Stickers



MADE IN CHINA

1PCS/PE BAG(0.06*80*90mm)+Stickers

NOTE:

1. UL1007 28# WIRE,PVC JACKET.
2. DB9F(BLUE INSULATOR,NICKEL PLATED)
3. DB 9M(BLUE INSULATOR,NICKEL PLATED) +nut
4. BLACK 45P PVC
5. SCREW IRON(27.0*5.9mm)

OPEN/SHORT TEST: 100% TEST.
INSULATIONS: 5M.

Company	CONRAD	Goods Code		Draw	Ling	Date	2013.9.7		D		
ITEM NO.		Drawing Evidence		Check		Date			C		
Goods NO.	29039c143			Approval		Date			B		
Original NO.		Unit(mm)							VER. A	REVISE	Date