


DVI Female

DVI Male



PIN ASSIGNMENT:

DVI Male	DVI Female
1-----	1
2-----	2
3-----	3
4-----	4
5-----	5
6-----	6
7-----	7
8-----	8
9-----	9
10-----	10
11-----	11
12-----	12
13-----	13
14-----	14
15-----	15
16-----	16
17-----	17
18-----	18
19-----	19
20-----	20
21-----	21
22-----	22
23-----	23
24-----	24
D1-----	D1
D2-----	D2
D3-----	D3
D4-----	D4
D5-----	D5
SHELL-----	SHELL

DVI24+5 Male To DVI24+5 Female 90° Adapter

①	Cable: 7/0.1 OD1.0 Wire
②	Connector: DVI24+5 Female Gold plated
③	Connector: DVI24+5 Male Gold plated
④	Moding:Black PVC molded

RoHS COMPLIANT

ELECTRONIC TEST:

- 1、 100% Open & Short Test
- 2、 Voltage:DC 300V 5M /10MS
- 3、 Contact Resistance:2 ohm max
- 4、 Insulation Resistance:10M ohm min

Company	CONRAD		Draw	FC065	Date	2012/05/05	C		
ITEM NO.	986562	Drawing Evidence	Check		Date		B		
Goods NO.			Approval		Date		A		
Original NO.		Unit(mm)						REVISE	Date