


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF 2DIRECT GMBH. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF 2DIRECT GMBH IS PROHIBITED.
WE RESERVE THE RIGHT TO MAKE TECHNICAL CHANGES. TECHNISCHE ÄNDERUNGEN VORBEHALTEN.

REVISIONS


REV	DESCRIPTION	DATE	APPROVED
A			



PIN OUT

USB3.0 A M

USB3.0 A M

SHELL BRAID+DRAIN SHELL

ITEM NO.	LENGYTH(MM)	TOLERANCE(MM)	CABLE BINDING(MM)	BAG SIZE(MM)	CARTON SIZE(MM)	CARTON Q'TY
CU0038	1000	±20	120*160*15	160*230	380*320*280	200
CU0039	2000	±40	110*140*20	160*230	380*320*240	120
CU0040	3000	±60	120*160*25	180*250	380*320*240	80

NOTES:

1. MATERIALS

1.1 CABLE 3.0: [7/0.12BCx1P+D(7/0.12BC)+AM+M]x2PCS+7/0.12TCx1P+7/0.12TCx2C+AM

+D(7/0.12BC)+B(16/6/0.12ALM)+BLACK PVC JACKET

OD: 5.0±0.15MM CABLE MARKING: USB 3.0 CABLE FULLY RATED 80" 30V


1.2 USB 3.0 A TYPE MALE: SOLDER TYPE,
GOLD FLASH CONTACTS, NICKEL PLATED SHELL.

1.3 ALL HOOD: MOLDED BLACK PVC.

2. TESTING: 100% OPEN AND SHORT TEST.

3. PACKING: 1PCS/PE BAG.

4. ALL MATERIAL BE REACH COMPLIANT.



PACKING: 1PCS/POLYBAG WITH LABEL



LABEL SIZE: 48*150MM

DIMENSIONAL TOLERANCES UNLESS OTHERWISE NOTED				APPROVALS		DATE		2direct GmbH						
TOLERANCE inch mm				DRAWN BY Xujun Yu		28/02/19								
.X				CHECKED BY				PRODUCT TITLE USB 3.0 CABLE, AM TO AM, BLACK						
.XX				APPROVED BY										
.XXX														
PROJECTION						CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY				ITEM NO.		DWG. NO.		REV. A
						COLOR VARIATIONS MAY OCCUR				SCALE: NONE		UNITS: mm	SHEET	/ 1