

# LogiLink®



## Wireless N 150Mbps USB Adapter

Art. No.: WL0084E

Space saving with fast data transfer rates up to 150 Mbps, supports IEEE 802.11b/g/n.  
Ideal for traveling

### Feature:

- » Complies with IEEE802.11n/g/b standards
- » High transfer data rate – up to 150Mbps
- » Supports 64/128-bit WEP, WPA, WPA2, WPA-PSK and WPA2-PSK Encryption
- » Supports WiFi Protection Setup (WPS)
- » Supports USB 2.0/1.1 interface
- » Supports Windows XP/Vista/7/8/10, Linux and MAC OS

### Specification:

Chipset Solution	Realtek RTL8188EUS
Standard	IEEE 802.11b/g/n, 1T1R mode
Interface Type	USB 2.0 /1.1
Frequency Band	2.4000~2.4835GHz (Industrial Scientific Medical Band)
Data Rate	For 802.11b/g: Peak rate 54Mbps, Peak throughput: 27Mbps For 802.11n: Peak rate: 150Mbps, Peak throughput: 90Mbps
Transmit Power	802.11b: 18dBm; 802.11g: 15dBm; 802.11n: 13dBm
Power Consumption	5V DC input, 130mA
Transmission Distance	Indoor up to 100m, outdoor up to 300m (Standard transmission distance, it is affected depending on different environment)
Security	64/128-bit WEP, WPA, WPA2, WPA-PSK and WPA2-PSK Encryption WiFi Protection Setup (WPS)
Supported OS	Windows XP/Vista/7/8/10, Linux 2.6.x and MAC OS
Dimension	6(H) x 13.5(W) x 23(D) mm
Temperature	Operating Temperature: 0°C~40°C Storage Temperature: -20~60°C
Humidity	Operating Humidity: 10%~85% non-condensing Storage Humidity: 5%~95% non-condensing

Best Connectivity



RoHS  
compliant



\* The specifications and pictures are subject to change without notice.  
\*All trade names referenced are the registered namework of their respective owners.



WL0084E



Made in China

# LogiLink®

## Wireless N 150Mbps USB Adapter

Art. No.: WL0084E



Please download the driver online at: <http://www.logilink.de/download/driver/WL0084E.zip>



### Package Contents:

- » 1 x Wireless N 150Mbps USB Adapter
- » 1 x Protector Cap
- » 1 x Quick Installation Guide

### Package Information:

- » Packing Dimension: 75 x 98 x 15mm
- » Packing Weight: 0.03kg
- » Carton Dimension: 492 x 320 x 145mm
- » Carton Q'ty: 120pcs
- » Carton Weight: 4.25kg



Made in China



RoHS  
compliant



\* The specifications and pictures are subject to change without notice.  
\* All trade names referenced are the registered namework of their respective owners.

Best Connectivity