



Art No. FAN104

Case Fan 120x120 with LED acryl

Specification:

- DC BRUSHLESS FAN
- BEARING TYPE: Sleeve
- RARTING VOLTAGE: DC 12V
- RATING CURRENT: $0.27A \pm 10\%$
- RATED POWER: $3.24 \pm 10\%W$
- OPERATION TEMPERATURE: BELOW 70 degrees
- OPERATION VOLTAGE: DC 9V-13V
- START VOLTAGE: $DC \leq 7V$
- ROTATE SPEED: $2000 \pm 10\%$ RPM
- MOST AIR FLOW: 75 CFM
- PERIOD OF USE: 30000-50000/H
- NOISE: 31.3 Db/a
- LEAD WIRE: 1007#26# 4pin wire, 280mm in length
- WEIGHT: 165G
- Dimension (mm): 120x120x25

Package Content:

- 1 x Case Fan

Packaging Information:

- Packing Dimension: 120x120x25 mm
- Packing Weight: 0.11kg
- Carton Dimension: 420x270x405 mm
- Carton Q'ty: 100pcs
- Carton Weight: 12kgs

* The specifications and pictures are subject to change without notice.
*All trade names referenced are the registered namework of their respective owners.



RoHS
compliant



Made in China