

									
Part number (color grey)	DN-19 FAN-2-WM-T	DN-19 FAN-2-WM-I	DN-19 FAN-1-WM-I	DN-19 FAN-2-HO	DN-19 FAN-4-HO	DN-19 FAN-2-N	DN-19 FAN-2-B-N	DN-19 FAN-4-SRV	DN-19 FAN-6-SRV
Part number (color black)	DN-19 FAN-2-WM-T-SW	⊗	⊗	DN-19 FAN-2-HO-SW	DN-19 FAN-4-HO-SW	DN-19 FAN-2-B-N	DN-19 FAN-4-B-N	DN-19 FAN-4-SRV-B	DN-19 FAN-6-SRV-B
Suitable cabinet series	19" Wall Mounting Unique 19" Wall Mounting Dynamic 19" Wall Mounting SOHO	19" Wall Mounting Outdoor (IP55)	19" Wall Mounting Outdoor (IP55)	all	all	19" Network Unique 19" Network- & Server Dynamic 19" Varioflex-N	19" Network Unique 19" Network- & Server Dynamic 19" Varioflex-N	19" Server Unique	19" Server Unique
Mounting area	Roof	Roof	Roof	19" profile rails Roof (varioFLEX)	19" profile rails Roof (varioFLEX)	Roof	Roof	Roof	Roof
Quality of fans	2	2	1	2	4	2	4	4	6
Air Flow	4.6 m³/min	4.6 m³/min	2.3 m³/min	4.6 m³/min	9.2 m³/min	4.6 m³/min	9.2 m³/min	9.2 m³/min	13.8 m³/min
Thermostat	Yes (Fixed)	Yes (Fixed)	Yes (Fixed)	Yes (Additional fixing bracket)	Yes (Additional fixing bracket)	Yes (Additional fixing bracket)	Yes (Additional fixing bracket)	Yes (Additional fixing bracket)	Yes (Additional fixing bracket)
Noise level	47 dBm	47 dBm	47 dBm	47 dBm	47 dBm	47 dBm	47 dBm	47 dBm	47 dBm
Switch	✓	✓	✓	✓	✓	✓	✓	✓	✓
Filters	⊗	✓	✓	⊗	⊗	⊗	⊗	⊗	⊗