

FOR A GOOD REASON
GRUNDIG



Profi Hairstyler HS 8980

Product data

- Unique 5x Ceramic Color Protector™
High-quality **5-times ceramic coating** of the styling attachments protects damaged hair, prolongs colour brilliance for dyed hair and provides even heat distribution as well as significantly smoother styles
- **Ionic technology** preserves natural hair moisture, helps prevent static and gives hair shine and volume. Hair is gently hydrated and vitalised
- 1200 Watt output for professional styling results at home
- **4 Styling attachments**
 - ø 50 mm attachment for volume, maxi curls and waves
 - ø 38 mm for volume and medium curls
 - ø 25 mm retractable brush for small curls and waves for easily removing without any ravling
 - styling nozzle: for hair drying
- Individual temperature settings
2 temperature and 2 air flow settings intended for fine, normal or thick hair to style and dry as well as a cool setting to fix hairstyles
- Great convenience in safety and use
 - 3,0 m cable with swivel joint
 - overheating protection
 - storage pouch
- Mains operation 230-240 V~, 50 Hz
- Color: titan / black



2 heat and 2 speed settings



4 styling attachments



Model number	HS 8980
Order number	GMN 0100
Packaging unit	6
Bar code	4013833618874
RRP*	

* recommended retail price of Grundig Intermedia GmbH