

FOR A GOOD REASON
GRUNDIG



Curls & Volume Hair Styler HS 5523

Product data

- max. 1100 Watt output
- Protects and cares with its gentle **ceramic coating with tourmaline** for hydrated hair with more shine, bounce and care:
 - Ceramic: ensures constant high temperature and even heat distribution
 - Tourmaline: generates negative ions in a natural way - prevents frizz, static charging and preserves the natural moisture of the hair
- **3 ceramic-tourmaline coated thermo brushes:**
 - ø 25mm for smaller curls and waves
 - ø 38mm for volume and medium curls
 - ø 50mm for volume, maxi curls and waves
- **Lockable cool setting** for long-lasting hair styling
- 2 heat and speed settings
- Swivel cord with hanging loop
- Air intake filter
- Also suitable for long hair
- Colour: tao blue high gloss/ silver



3 Thermo brushes

ETW TESTMAGAZIN - RESULT	
Grundig Curls & Volume Hairstyler HS 5523 <small>* structurally identical model</small>	
GOOD	84,6 %
Curls hairstyler tested	11/2009
„Persons who wish to get voluminous curls are proper with HS 5523.“	
„Thanks to the Hot Air Styler the hair can be dried and styled in one go.“	
„Testing results are convincingly!“	
<small>* structurally identical with tested model Grundig HS 5520</small>	



2 Heat- / speed settings



4 013833 621522

Model number	HS 5523
Order number	GMK 7920
Packaging unit	6
Bar code	4013833621522
RRP*	

* recommended retail price