

High Frequency Battery Charger

FEATURES :

- Charges All Types of Lead Acid Battery
- Complete Circuit Safety Protection
- Fully Automatic
- Microprocessor Programming

powerchairs pallet trucks lift trucks industrial cleaning machines electric vehicles platforms



■ Automated Testing System



■ Burn-in Test



■ Charger Design



■ Production Line



No. 1-7, Gongjian Rd., Cidu District,
Keelung City 20647, Taiwan R.O.C.
Tel: +886-2-2452 2431 Fax: +886-2-2452 2559
e-mail : sales@cte.com.tw

- ※ TS-16949
- ※ ISO-9001
- ※ QS-9000
- ※ ISO-14001

<http://www.ctetech.com.tw>

ON BOARD SEALED CHARGER SERIES



Model	Output Voltage	Charge Current	Input Voltage	FAN	Dimensions (mm)
4C24020A	24V	2A	100~240VAC, 50/60 HZ	No	L110xW60xH36

Certification



Model	Output Voltage	Charge Current	Input Voltage	FAN	Dimensions (mm)
4C24030A	24V	3A	110/220VAC, 50/60 HZ	No	L190xW100xH55
4C24040A	24V	4A	110/220VAC, 50/60 HZ	No	L190xW100xH55

Certification



Model	Output Voltage	Charge Current	Input Voltage	FAN	Dimensions (mm)
4C24050A	24V	5A	100~240VAC, 50/60 HZ	No	L177xW118xH68

Certification

OFF BOARD CHARGER (WITHOUT FAN) SERIES



Model	Output Voltage	Charge Current	Input Voltage	FAN	Dimensions (mm)
4C12020	12V	2A	100~240VAC, 50/60 HZ	No	L140xW76xH44
4C12030	12V	3A	100~240VAC, 50/60 HZ	No	L140xW76xH44
4C24020	24V	2A	100~240VAC, 50/60 HZ	No	L140xW76xH44


Certification



Model	Output Voltage	Charge Current	Input Voltage	FAN	Dimensions (mm)
4C24080A	24V	8A	100~240VAC, 50/60 HZ	No	L185xW130xH185

Certification

MEDICAL SAFETY STANDARD CHARGER SERIES



Model	Output Voltage	Charge Current	Input Voltage	FAN	Dimensions (mm)
4C24020A	24V	2A	100~240VAC, 50/60 HZ	No	L110xW60xH36

Certification



Model	Output Voltage	Charge Current	Input Voltage	FAN	Dimensions (mm)
4F24040	24V	4A	110/220VAC, 50/60 HZ	Yes	L190xW100xH55
4F24050	24V	5A	110/220VAC, 50/60 HZ	Yes	L190xW100xH55
4F24060	24V	6A	110/220VAC, 50/60 HZ	Yes	L190xW100xH55

Certification

INDUSTRIAL ELECTRONIC CHARGER SERIES



Model	Output Voltage	Charge Current	Input Voltage	FAN	Dimensions (mm)
4C24300	24V	20-30A	110/220VAC, 50/60 HZ	Yes	227xW159xH98
4C36250	36V	15-30A	110/220VAC, 50/60 HZ	Yes	227xW159xH98
4C48250	48V	20-25A	110/220VAC, 50/60 HZ	Yes	227xW159xH98

Certification