

41509



RDW

Vehicle Technology Division



THE NETHERLANDS
(NEDERLAND)



COMMUNICATION


Concerning:

- approval granted
- ~~- approval extended~~
- ~~- approval refused~~
- ~~- approval withdrawn~~
- ~~- production definitely discontinued~~

of a type of rear fog lamp for power-driven vehicles and their trailers pursuant to Regulation number 38.

Approval number: E4-38R-00 4053

Extension number: 00

1. Trade name or mark of the device : 
2. Manufacturer's name for the type of device : DF-TRL009
3. Manufacturer's name and address : Zhejiang Dahao Automotive Co., Ltd.
Xiaotian, Duqiao, Linhai,
Taizhou City Zhejiang, 317016,
China
4. If applicable, name and address of the manufacturer's representative : --
5. Submitted for approval on : 2 August 2011
6. Technical service responsible for conducting approval tests : DEKRA Certification B.V.
7. Date of report issued by that service : 22 August 2011
8. Number of reports issued by that service : 2146434-PHO 11-131-27
9. Concise description: Category F1 Rear Fog Lamp




P.O. Box 777
2700 AT Zoetermeer
The Netherlands



Tel. +31 (0)79 345 81 43
Fax +31 (0)79 345 80 43
www.rdw.nl

Vehicle Approval and Information

Approval number: E4-38R-00 4053

Extension number: 00

- Number, category and kind of light source(s) : 19 x non replaceable light source (LEDs)
- Voltage and wattage : 12V; 2W
- Light source module specific identification code : --
- Geometrical conditions of installation and relating variations, if any : --
- Application of an electronic light source control gear/variable intensity control:
- (a) Being part of the lamp : yes/no
- (b) Being not part of the lamp : yes/no
- Input voltage(s) supplied by an electronic light source control gear/variable intensity control : --
- Electronic light source control gear/variable intensity control manufacturer and identification number (when the light source control gear is part of the lamp but is not included into the lamp body) : --
- Variable luminous intensity : yes/no
10. Position of the approval mark : See annexed drawing
11. Reason(s) for extension (if applicable) : --
12. Approval : granted/extended/refused/withdrawn
13. Place : Zoetermeer
14. Date : 31-AUG-2011
15. Signature : 
16. The list of documents deposited with the Administrative Service which has granted approval is annexed to this communication and may be obtained on request.
- 2 drawings No. DF-TRL009 and Determination of the apparent surface (annexed)
 - Test report as mentioned in item 8.



设计	审核	批准	日期	比例	图号	图名
浙江大豪汽车有限公司 Zhejiang Dahao Automotive Co., Ltd.				浙江大豪汽车有限公司 DF-TRL009		



Approval number: E4-38R-00 4053

Extension number: 00

Determination of the apparent surface

