



NOTE:  
1. MATERIAL

- 1.1 CABLE: 27AWG BC\*4+BRAID SHIELD(16/5/0.12ALM)+LSZH JACKET  
CABLE MARKING:Logilink S/FTP CAT6 27AWGx4P PIMF PATCH ISO/IEC 11801 & EN 50173 VERIFIED HALOGEN FREE
- 1.2 CONNECTER: RJ45(8P8C) MALE CAT6 TYPE, WITH SHIELD; (ONE-PIECE)  
INSULATION: CLEAR RED POLYESTER, UL94V-2  
CONTACTS:BRASS, GOLD PLATED 3u'  
SHIELD: STEEL, NICKEL PLATED.
- 1.3 PVC MOLDING: PVC
- 1.4 ALL COMPONENTS ARE ROHS COMPLIANT.
2. ELECTRICAL
- 2.1 100% OPEN AND SHORT TEST



SECTION A-A



Length	Tolerance	CQ2xx1S	white
≤1000mm	±30mm	CQ2xx2S	grey
1000<L≤5000mm	±50mm	CQ2xx3S	black
5000<L≤10000mm	±100mm	CQ2xx4S	red
10000<L≤20000mm	±200mm	CQ2xx5S	green
20000mm<L	±500mm	CQ2xx6S	blue

Tolerance	SCALE:
X. ±0.5	FREE
.X ±0.3	
.XX ±0.10	UNIT:

Angle:	mm
.X ±3°	
.X ±1°	

REV.	DESCRIPTION	DATE	REV.	DESCRIPTION	DATE
00	DESCRIPTION	2013-8-14	X	±3°	00

**Logilink Professional**

CAT.6 S/FTP Primeline

DWG. No. : 2D-PC13081408  
TITLE: 27AWG S/FTP CAT6 PATCH CABLE

Approved by  
PC13081408

Checked by

Design by  
PC13081408