

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>ÖLFLEX® PLUG Extension Cable 540 P safety yellow*</b>	73222337 18.11.2013

Earthing-type extension cable with straight plug and coupling



### Application range

Mechanical engineering  
Construction industry  
Agricultural equipment  
In damp interiors or outdoors



### Design

Mounted, straight earthing-type plug (16 amp., 250 V, solid rubber, colour: black) in accordance with DIN 49440/441, protection rating: IP 44

Mounted, straight earthing-type coupling with rubber cover (16 A, 250 V, solid rubber, colour: black) in accordance with DIN 49440/441, protection rating: IP 44

### Product features

Other lengths, customised versions, cable types and plug versions are available upon request  
Customised printing is available upon request

### Remark

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

\* Trade product, no Lapp product

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

Number of cores and mm <sup>2</sup> per conductor:	3 G 1,5
Outer diameter (mm):	8,9
Length (m):	5
Copper index kg/1.000 pieces:	215
Nominal voltage:	U0: 250 V AC

Product Management	Document: ÖLFLEX® PLUG Extension Cable 540 P safety yellow*	1 / 1
--------------------	---	-------