



DATA SHEET	22260722
AB-C5-M12MS-PB-TR	valid from: 05.11.2009

Terminating resistor PROFIBUS M12



Technical data

Lapp article number:	22260722
Nominal current I_N :	4 A
Nominal voltage U_N :	60 V
Number of poles:	4
Coding:	B - inverse
Contact resistance:	5 m Ω
Ambient temp. min. (operation)- plug/socket:	-25 °C
Ambient temp. max. (operation)- plug/socket:	90 °C
Surge voltage category:	II
Pollution degree:	3
Degree of protection:	IP65/IP67/IP69K
Status display:	No
Contact carrier material:	TPU GF
Contact surface material:	Ni/Au
Material of grip body:	TPU, hardly inflammable, self- extinguishing
Material, knurls:	Zinc die-cast, (nickel-plated)
Inflammability class acc. to UL 94:	HB

