

| | | |
|-------------------|--|--|
| U.I. Lapp GmbH | DATASHEET |  |
| | Conductor end sleeves insulated | 61746720 14.11.2013 |

Conductor end sleeves with insulation for cabinet builders , according to DIN or German colour code, CSA approved, halogen-free



Halogen-free

Application range

Control cabinets and equipment wiring

Benefits

Funnel-shaped opening makes it easy to slip them onto the strands
The conductor is permanently connected to the collar by crimping

Norm references / Approvals

All DIN conductor end-sleeves are in accordance with DIN 46228 Part 4
CSA approved, File-Number: LR 105629-1

Remark

K = short; N = medium; HL = large; L = extra large; Other sizes and colours are available upon request
Photographs are not to scale and do not represent detailed images of the respective products.

*Under some circumstances the end sleeves withstand temperatures under -5°C. Please contact Lapp Kabel to clarify the specific application area.

Technical Data

| | |
|-----------------------|----------------------------------|
| Article designation: | AHI L 1,5/18 |
| For mm ² : | 1,5 |
| AWG: | 16 |
| Colour: | red |
| l1 mm: | 24.5 |
| l2 mm: | 18 |
| d 1 mm: | 1.8 |
| s1 mm: | 0.15 |
| d 2 mm: | 3.4 |
| s2 mm: | 0.3 |
| Pieces / PU: | 500 |
| Note: | Halogen-free |
| Material: | Copper/PP Surface: tin-plated |
| Temperature range: | -5°C to +105°C* |



| | | |
|--------------------|---|-------|
| Product Management | Document: Conductor end sleeves insulated | 1 / 2 |
|--------------------|---|-------|

| | | |
|-------------------|--|--|
| U.I. Lapp GmbH | <h1>DATASHEET</h1> |  |
| | Conductor end sleeves insulated | 61746720 14.11.2013 |



| | | |
|--------------------|---|-------|
| Product Management | Document: Conductor end sleeves insulated | 2 / 2 |
|--------------------|---|-------|