These connectors are attractive because of their compact housing.
Small and space-saving for narrow available space




Industrial machinery and plant engineering

Mechanical resistance

Robust

Waterproof

## Info
Compact, robust metal housings size H-A 10

## Application range
Machine and equipment manufacturing
Control engineering
Electronic laboratory

## Product features
Hood, low version
Bolts for single lever
Straight cable entry
Versions with / without neck

## Remark
Photographs are not to scale and do not represent detailed images of the respective products.


## Technical Data


| | |
|---|---|
| Article: | H-A 10 TG M25 |
| M: | 25 |
| Pieces / PU: | 5 |
| Material: | Housing: aluminium alloy, grey<br>Lever: zinc-plated steel<br>Sealing: NBR |
| Protection rating: | IP 65 (latched) |
| Temperature range: | -40 °C to +100 °C, short-term up to +125 °C |



PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.







PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.