These connectors are attractive because of their compact housing.
Small and space-saving for narrow available space



Industrial machinery and plant engineering

Mechanical resistance

Robust

Waterproof

Info
Compact, robust metal housings size H-A 10

Application range
Machine and equipment manufacturing
Control engineering
Electronic laboratory


Product features
Hood, low version
Bolts for single lever
Side cable entry
Versions with neck

Remark
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	H-A 10 TS M25
M:	25
Neck:	yes
Pieces / PU:	5
Material:	Housing: aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.



PN 0486/01_03.10
©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.