## DATASHEET



## EPIC® H-B 10 TG

10040100 14.11.2013

Housing design H-B. The industry standard.

The smallest housing with single and double lever. The right housing is available for every application





Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 10

#### Application range

Plant engineering Light & sound technology Plastics industry

#### **Product features**

Hood, low version Bolts for double lever Straight cable entry Versions with / without neck

#### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

#### **Technical Data**

Article:	H-B 10 TG 21
PG:	21
Neck:	yes
Pieces / PU:	10
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

EPIC	

Product Management	Document: EPIC® H-B 10 TG	1 / 2
PN 0486/01_03.10 Photographs are not to scale and do not represent	©2012 Lapp Group - Technical changes reserved detailed images of the respective products.	


# DATASHEET



### EPIC® H-B 10 TG

10040100 14.11.2013

EPIC®



Product Management	Document: EPIC® H-B 10 TG	2/2
PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved Photographs are not to scale and do not represent detailed images of the respective products.		