DATASHEET



EPIC® H-B 16 TBFH-LB

79092200 14.11.2013

Housing design H-B. The industry standard. The housing standard. Wide choice for all applications





Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 16

Application range

Plant engineering Light & sound technology Plastics industry

Product features

Cable coupler hood, high version Single lever Straight cable entry Versions with / without neck

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data Article:	H-B 16 TBFH-LB M25
M:	25
Pieces / PU:	5
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 $^{\circ}\text{C}$ to +100 $^{\circ}\text{C},$ short-term up to +125 $^{\circ}\text{C}$



Product Management	Document: EPIC® H-B 16 TBFH-LB	1 / 2
DN 0494 /01 02 10	©2012 Lapp Group Technical changes reserved	

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved Photographs are not to scale and do not represent detailed images of the respective products.

DATASHEET



3°

EPIC® H-B 16 TBFH-LB

79092200 14.11.2013

Image: space of the space o

Product Management	Document: EPIC® H-B 16 TBFH-LB	2/2
PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved Photographs are not to scale and do not represent detailed images of the respective products.		