U.I. Lapp **DATASHEET ® LAPP GROUP** GmbH 79105400 **EPIC® H-B 16 TGBH** 14.11.2013

Housing design H-B. The industry standard. The housing standard. Wide choice for all applications









Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 16

Application range

Plant engineering Light & sound technology Plastics industry

Product features

Hood, high version **Dual levers** Straight cable entry Versions with / without neck

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article: H-B 16TGBH M32

M: 32 Pieces / PU: 5

Material: Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel


Sealing: NBR

Protection rating: IP 65 (latched)

-40 °C to +100 °C, short-term up to +125 °C Temperature range:

Product Management	Document: EPIC® H-B 16 TGBH	1/2
--------------------	-----------------------------	-----

U.I. Lapp GmbH	DATASHEET	EAPP GROUP
	EPIC® H-B 16 TGBH	79105400
		14.11.2013



Product Management	Document: EPIC® H-B 16 TGBH	2/2
--------------------	-----------------------------	-----