DATASHEET



EPIC® H-B 16 TGH 2X

79128600 14.11.2013

Housing design H-B. The industry standard. The housing standard. Wide choice for all applications





Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 16

Application range

Plant engineering Light & sound technology Plastics industry

Product features

Hood, high version Bolts for double lever 2 straight cable entries Versions without neck

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical	Data
Article	

Article:		
M:		
Pieces / PU:		
Material:		

Protection rating:

Temperature range:



H-B 16 TGH 2XM32

2 x 32

5 Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR IP 65 (latched) -40 °C to +100 °C, short-term up to +125 °C

Product Management Document: EPIC® H-B 16 TGH 2X

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved Photographs are not to scale and do not represent detailed images of the respective products.


DATASHEET



EPIC® H-B 16 TGH 2X

79128600

14.11.2013



Product Management	Document: EPIC® H-B 16 TGH 2X	2/2
PN 0486/01_03.10 Photographs are not to scale and do not represent	©2012 Lapp Group - Technical changes reserved detailed images of the respective products.	