DATASHEET



EPIC® H-B 16 TGH

79100400 14.11.2013

Housing design H-B. The industry standard. The housing standard. Wide choice for all applications





Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 16

Application range

Plant engineering Light & sound technology Plastics industry

Product features

Hood, high version Bolts for double lever Straight cable entry Versions with / without neck

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

| Technical | Data |
|-----------|------|
| Article | |

| Article: | |
|--------------|--|
| M: | |
| Pieces / PU: | |
| Material: | |
| | |

Protection rating:

Temperature range:



H-B 16 TGH M32

32

5 Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR IP 65 (latched) -40 °C to +100 °C, short-term up to +125 °C

| Product Management | Document: EPIC® H-B 16 TGH | 1 / 2 |
|---|--|-------|
| PN 0486/01_03.10 Photographs are not to scale and do not represent | ©2012 Lapp Group - Technical changes reserved detailed images of the respective products. | |

DATASHEET





EPIC® H-B 16 TGH

79100400

14.11.2013







| Product Management | Document: EPIC® H-B 16 TGH | 2/2 |
|---|--|-----|
| PN 0486/01_03.10 Photographs are not to scale and do not represent | ©2012 Lapp Group - Technical changes reserved detailed images of the respective products. | |