U.I. Lapp **DATASHEET ® LAPP GROUP** GmbH 79094200 **EPIC® H-B 16 TGH-RO** 14.11.2013

Housing design H-B. The industry standard. The housing standard. Wide choice for all applications









Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 16

Application range

Plant engineering Light & sound technology Plastics industry

Product features

Hood, high version Reels for single lever Straight cable entry Versions with / without neck

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article: H-B 16 TGH-RO M25

M: 25 Pieces / PU: 5

Material: Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel

Sealing: NBR

Protection rating: IP 65 (latched)

-40 °C to +100 °C, short-term up to +125 °C Temperature range:

Product Management Document: EPIC® H-B 16 TGH-RO	1 / 2
--	-------

U.I. Lapp GmbH	DATASHEET	LAPP GROUP
	EPIC® H-B 16 TGH-RO	79094200
		14.11.2013

