Housing design H-B. The industry standard.
Ideal for many applications due to a wide range of housings and inserts



Automation

Industrial machinery and plant engineering

Mechanical resistance

Robust

Waterproof

Info
Universal, robust metal housings size H-B 24

Application range
Plant engineering
Light & sound technology
Plastics industry


Product features
Hood, low version
Dual levers
Side cable entry
Versions with neck

Remark
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	H-B 24 TSB M32
M:	32
Neck:	yes
Pieces / PU:	5
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.



PN 0486/01_03.10
©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.