

U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	EPIC® H-B 6 AG-LB	10003000 14.11.2013

Housing design H-B. The industry standard.
The smallest housing out of the H-B series. For inserts with high electrical properties



Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 6

Application range

Plant engineering
Control engineering
Plastics industry

Product features

Panel-mount base
Single lever
Included: flat gasket

Remark


Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	H-B 6 AG-LB
Pieces / PU:	10
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Product Management	Document: EPIC® H-B 6 AG-LB	1 / 2
--------------------	-----------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	EPIC® H-B 6 AG-LB	10003000 14.11.2013



Product Management	Document: EPIC® H-B 6 AG-LB	2 / 2
--------------------	-----------------------------	-------