




DATA SHEET	63101020
Receptacles rolled type 0,1 - 6 mm²	valid from : 18.12.2003

Technical data:

- Brass
- Tin plates
- Brazed barrel
- polycarbonate insulation
- easy-entry
- not for solid conductors

For more safety on site all insulated connectors have an imprint that indicates the cross section of the respective connector.
The crimping dies of the recommended tool emboss the cross section of the used die onto the connector insulation.

Easy-entry:
The insulation has an easy-entry device, which assures correct insertion of the conductor into the cable socket.



Receptacles rolled type 0,1 - 6 mm²

mm ²	Cat no	mm W	d	L	For tabs	s	g/ 100	Note
0,1-0,5	on request	3,7	2,3	16,0	2,8x0,5	7	32	3,4
	on request	*	*	*	2,8x0,8	*	*	3,4
0,5-1,5	63101020	3,5	3,3	18,5	2,8x0,5	7	60	
	63101010	*	*	*	2,8x0,8	*	*	
	63101030	5,7	3,7	19,0	4,8x0,5	*	83	2, 4
	63101040	*	*	*	4,8x0,8	*	82	2, 4
	63101050	7,6	4,0	20	6,3x0,8	*	96	
	on request	*	*	*	*	*	99	1
1,5-2,5	63101060	5,7	4,4	19,0	4,8x0,5	8	91	2, 4
	63101070	*	*	*	4,8x0,8	*	87	2, 4
	63101080	7,6	4,5	20	6,3x0,8	*	106	
	on request	*	*	*	*	*	110	1
	on request	9,1	4,3	24	8,4x0,8	*	135	2,4
4-6	on request	7,6	6,4	24	6,3x0,8	9	183	
	on request	11,0	6,2	31	9,5x1,2	*	233	2,4