

Technical data:


- electrolytic copper
- tin plated
- brazed barrel
- polycarbonate insulation
- easy-entry
- not for solid conductors

For more safety on site all insulated connectors have an imprint that indicates the cross section of the respective connector.

The crimping dies of the recommended tool emboss the cross section of the used die onto the connector insulation.

Easy-entry:

The insulation has an easy-entry device, which assures correct insertion of the conductor into the cable socket.



Fork terminals 0,1 - 6 mm²

mm ²		Cat no	mm W	d	t	L ₁	L	s	g/ 100	Note
0,1-0,5		M3 on request	5,0	2,0	0,5	14,0	16,0	6	24	3
0,25-0,75		M3 63105010	5,5	3,2	0,5	15,0	18,0	7	41	
		M3,5 on request	6,2	«	«	17,5	21	«	«	
		M4 63105020	7,5	«	«	«	«	«	«	
0,5-1,5		M3 63105040	5,5	4,0	0,7	16	19	7	64	
		M3,5 on request	6	«	«	«	«	«	66	
		M3,5 on request	5,5	«	«	17,5	21	«	62	
		M4 63105050	7	«	«	17	20,5	«	64	
		M5 63105060	9	«	«	18	22,5	«	75	
		M6 63105070	11	«	«	21	26,5	«	90	
1,5-2,5		M3 63105110	5,5	4,5	0,8	16	19	8	72	
		M3,5 63105120	6	«	«	«	«	«	87	
		M3,5 on request	5,5	«	«	17,5	21	«	81	
		M4 63105120	7	«	«	17	20,5	«	84	
		M5 63105140	9	«	«	18	22,5	«	96	
		M6 63105150	11	«	«	21	26,5	«	113	
4-6		M4 63105210	8	6,4	1,0	20,5	24	9	159	
		M5 63105520	9	«	«	«	25	«	161	
		M6 63105230	11	«	«	23	28,5	«	174	
		M8 on request	14	«	«	24	31	«	207	
		M10 on request	18,0	«	«	27	36	«	280	

