
These connectors are attractive because of their compact housing.
Small and space-saving for narrow available space



Industrial machinery and plant engineering

Mechanical resistance

Robust

Waterproof

Info
Compact, robust metal housings size H-A 10

Application range
Machine and equipment manufacturing
Control engineering
Electronic laboratory


Product features
Panel-mount base
Single lever
Metal cover
Included: flat gasket

Remark
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	H-A 10 AD-LB
Pieces / PU:	5
Material:	Housing: aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.



PN 0486/01_03.10
©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.