

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>EPIC® H-A 10 TSH</b>	79462200 14.11.2013

These connectors are attractive because of their compact housing.  
Small and space-saving for narrow available space



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

#### Info

Compact, robust metal housings size H-A 10

#### Application range

Machine and equipment manufacturing  
Control engineering  
Electronic laboratory

#### Product features

Hood, high version  
Bolts for single lever  
Side cable entry  
Versions with / without neck

#### Remark



Photographs are not to scale and do not represent detailed images of the respective products.

#### Technical Data

Article:	H-A 10 TSH M20
M:	20
Pieces / PU:	5
Material:	Housing: aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Product Management	Document: EPIC® H-A 10 TSH	1 / 2
--------------------	----------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 <b>LAPP GROUP</b>
	<b>EPIC® H-A 10 TSH</b>	79462200 14.11.2013



Product Management	Document: EPIC® H-A 10 TSH	2 / 2
--------------------	----------------------------	-------