# U.I. Lapp GmbH DATASHEET EPIC® H-A 16 SGRL-LB 10568100 14.11.2013

These connectors are attractive because of their compact housing. Small and compact, for applications with high number of contacts







Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

### Info

Compact, robust metal housings size H-A 16

# **Application range**

Machine and equipment manufacturing Control engineering Electronic laboratory

#### **Product features**

Surface-mount base Single lever 2 cable entries

## Remark

Photographs are not to scale and do not represent detailed images of the respective products.

#### **Technical Data**

Article: H-A 16 SGRL-LB 16

PG: 16 Pieces / PU: 5

Material: Housing: aluminium alloy, grey

Lever: zinc-plated steel


Sealing: NBR

Protection rating: IP 65 (latched)

Temperature range: -40 °C to +100 °C, short-term up to +125 °C

Product Management	Document: EPIC® H-A 16 SGRL-LB	1/2
--------------------	--------------------------------	-----

U.I. Lapp GmbH	DATASHEET	LAPP GROUP
	EPIC® H-A 16 SGRL-LB	10568100
	EPIC® H-A 10 SGNL-LB	14.11.2013



Product Management	Document: EPIC® H-A 16 SGRL-LB	2/2
--------------------	--------------------------------	-----