
These connectors are attractive because of their compact housing.
Small and compact, for applications with high number of contacts



Industrial machinery and plant engineering

Mechanical resistance

Robust

Waterproof

Info
Compact, robust metal housings size H-A 16

Application range
Machine and equipment manufacturing
Control engineering
Electronic laboratory

Product features
Cable coupler hood, high version
Single lever
Straight cable entry
Versions with / without neck


Remark
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	H-A 16 TBFH-LB M20
M:	20
Pieces / PU:	5
Material:	Housing: aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.





PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.