
Housing design H-B. The industry standard.
The smallest housing with single and double lever. The right housing is available for every application



Automation

Industrial machinery and plant engineering

Mechanical resistance

Robust

Waterproof

Info
Universal, robust metal housings size H-B 10

Application range
Plant engineering
Light & sound technology
Plastics industry


Product features
Surface-mount base, low version
Bolts for double lever
1 cable entry
Metal cover

Remark
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	H-B 10 SDR-BO M20
M:	20
Pieces / PU:	10
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.



PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.