
Housing design H-B. The industry standard.
The smallest housing with single and double lever. The right housing is available for every application



Automation

Industrial machinery and plant engineering

Mechanical resistance

Robust

Waterproof

## Info
Universal, robust metal housings size H-B 10

## Application range
Plant engineering
Light & sound technology
Plastics industry

## Product features
Surface-mount base, high version
Dual levers
1 cable entry


## Remark
Photographs are not to scale and do not represent detailed images of the respective products.

## Technical Data

| | |
|---|---|
| Article: | H-B 10 SGRH M32 |
| M: | 32 |
| Pieces / PU: | 10 |
| Material: | Housing: powder-coated aluminium alloy, grey<br>Lever: zinc-plated steel<br>Sealing: NBR |
| Protection rating: | IP 65 (latched) |
| Temperature range: | -40 °C to +100 °C, short-term up to +125 °C |




PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.






PN 0486/01_03.10
©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.