

U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	<b>EPIC® H-B 10 SGRH-LB</b>	79060200 14.11.2013

Housing design H-B. The industry standard.  
The smallest housing with single and double lever. The right housing is available for every application



Automation



Industrial machinery and plant engineering




Mechanical resistance



Robust



Waterproof



### Info

Universal, robust metal housings size H-B 10

### Application range

Plant engineering  
Light & sound technology  
Plastics industry

### Product features

Surface-mount base, high version  
Single lever  
1 cable entry

### Remark


Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data

Article:	H-B 10 SGRH-LB M25
M:	25
Pieces / PU:	10
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Product Management	Document: EPIC® H-B 10 SGRH-LB	1 / 2
--------------------	--------------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 <b>LAPP GROUP</b>
	<b>EPIC® H-B 10 SGRH-LB</b>	79060200 14.11.2013



Product Management	Document: EPIC® H-B 10 SGRH-LB	2 / 2
--------------------	--------------------------------	-------