U.I. Lapp GmbH DATASHEET EPIC® H-B 10 TGH 70050600 14.11.2013

Housing design H-B. The industry standard.

The smallest housing with single and double lever. The right housing is available for every application







Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 10

Application range

Plant engineering Light & sound technology Plastics industry

Product features

Hood, high version Bolts for double lever Straight cable entry Versions with / without neck

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article: H-B 10 TGH 29

PG: 29
Neck: yes
Pieces / PU: 10

Material: Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel

Sealing: NBR

Protection rating: IP 65 (latched)

Temperature range: $-40 \, ^{\circ}\text{C}$ to $+100 \, ^{\circ}\text{C}$, short-term up to $+125 \, ^{\circ}\text{C}$

Product Management	Document: EPIC® H-B 10 TGH	1/2
--------------------	----------------------------	-----

U.I. Lapp GmbH	DATASHEET	EXAPP GROUP
	EPIC® H-B 10 TGH	70050600
		14.11.2013

