

Housing design H-B. The industry standard.

The smallest housing with single and double lever. The right housing is available for every application







Automation



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Universal, robust metal housings size H-B 10

Application range

Plant engineering Light & sound technology Plastics industry

Product features

Hood, high version Bolts for double lever Side cable entry Versions with / without neck

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article: H-B 10 TSH M32

M: 32 Pieces / PU: 10

Material: Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel


Sealing: NBR

Protection rating: IP 65 (latched)

Temperature range: -40 °C to +100 °C, short-term up to +125 °C

Product Management	Document: EPIC® H-B 10 TSH	1/2
--------------------	----------------------------	-----

U.I. Lapp GmbH	DATASHEET	EXAPP GROUP
	EPIC® H-B 10 TSH	79052600
		14.11.2013



Product Management Doc	cument: EPIC® H-B 10 TSH	2/2
------------------------	--------------------------	-----