Housing design H-B. The industry standard.
Ideal for many applications due to a wide range of housings and inserts



Automation

Industrial machinery and plant engineering

Mechanical resistance

Robust

Waterproof

Info
Universal, robust metal housings size H-B 24

Application range
Plant engineering
Light & sound technology
Plastics industry

Product features
Hood, high version
Bolts for double lever
Straight cable entry
Versions with / without neck


Remark
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article:	H-B 24 TGH M25
M:	25
Pieces / PU:	5
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.





PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.