

DATA SHEET	160xxxx
NYM-O-J	valid from : 01.09.2000

Application

NYM are single or multicore PVC sheathed cables intended for fixed installation over, on, in and under the plastering in dry, damp and wet locations as well as in masonry and concrete, but not for direct embedding of compressed and vibrated concrete. They are suitable for outdoor use, if there is a protection of sunlight.

Design

Core Identification colour-coded up to 5 cores in acc. to VDE 0293 (HD 186), more than 5 cores black with white numbers, with or without gn/ye earth conductor.

Electrical properties at 20° C

Nominal voltage 300/500 V

Test voltage 2000 V

Mechanical and thermal properties

Temperature range for
 fixed installation: - 40 °C up to + 70 °C
 during installation: - 5 °C up to + 60 °C
 at conductor: max. + 70 °C

Flame retardant acc. to IEC 60 332.1 resp. VDE 0482 Teil 265-2-1

Approval The cables are approved in accordance to VDE 0250 part 204. Marking is effected by imprinting / embossing of the jacket or by the black-red VDE identification thread.

EC directive This cable confirms to ECD 73/23/EEC (low voltage directive).

elaborated by: TE-K: N. Ensslen / M. Herb	Document: DB1600000_2EN	page 1 of 1
--	--	-------------