Uninsulated cable lugs/solderless terminals according to DIN 46234, high-quality electrolytic copper for good conductivity, least resistance

Application range
For cables with category 2,5 and 6 conductors
Manufacturing of control cabinets and equipment
Trains and buses

Benefits
For first-class connection with simple operating principle
Thus providing the best electrical conductivity (least resistance)

Norm references / Approvals
In accordance with VG 88710
Coil form DIN 46234, non-insulated

Note
For processing tools see the keyword index "crimping pliers for other connections"

Remark
Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation:	KB2,5-10R DIN 46234
For mm²:	1,5 - 2,5
UL approval:	no
AWG:	16-14
Nominal size:	10-2,5
d1:	10.5
d3:	14
l1:	17
a1:	5
s:	0.8
Pieces / PU:	100
Note:	s = thickness of material
Material:	High-quality electrolytic copper for good conductivity
Temperature range:	Max. temperature: +120 °C (short-term)

PN 0486/01_03.10 ©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.



PN 0486/01_03.10
©2012 Lapp Group - Technical changes reserved
Photographs are not to scale and do not represent detailed images of the respective products.