



DATA SHEET	52100320
SKINDICHT® A-PG/M	valid from : 27.04.2004

The SKINDICHT® A-PG/M is a polyamide glass fibre reinforced converter from a PG outer thread to a metric inner thread.



Technical features:

Connecting thread:	PG 7 to PG 48 in acc. to DIN 40 430
Inside thread:	M 12 x 1.5 to M 63 x 1,5 in acc. to DIN 60 423 Tab.1
Material:	Polyamide, glass fibre reinforced
Temperature range:	- 25°C to +80°C
Standard colour:	RAL 7035 light grey

For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

Elaborated by : TE-VZ: D. Müller	Document: DB52100320EN	page 1 of 1
-------------------------------------	------------------------	-------------