

U.I. Lapp GmbH	DATASHEET	
	SKINDICHT® BLK-M	52006670 14.11.2013

For closing pre-threaded holes
Cost-effective solution



Reliability



UV-resistant



Waterproof

Info

SKINDICHT® BLK-M/BLK-GL-M will be renamed into SKINTOP® PLUG

Application range

Control cabinet manufacturing
Distribution box
Junction boxes

Design

Metric connection thread acc. to EN 50262

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Technical Data

Article designation / size:	63 x 1,5
Thread length, D (mm):	12
Pieces / PU:	25
On request:	BLK-M with O-ring, black RAL 9005
Colour delivered:	Light grey (RAL 7035)
Material:	Impact-resistant polystyrene
Protection rating:	IP 54 IP 68 with O-ring
Temperature range:	-25°C to +60°C

Product Management	Document: SKINDICHT® BLK-M	1 / 1
--------------------	----------------------------	-------